

## Equivalences des ventilateurs à filtre et grilles de sortie Sarel série 17000 avec Pfannenberg

**Tableau n°1 : Classement par ordre croissant des références Sarel**

REFERENCE SAREL	REFERENCE PFANNENBERG
17883	PF2500 IP54 115VAC
17884	PF3000 IP54 115VAC
17885	PF5000 IP54 115VAC
17886	PF6000 IP54 115VAC
17887	PF2500 IP55 115VAC
17889	PF3000 IP55 115VAC
17890	PF5000 IP55 115VAC
17891	PF6000 IP55 115VAC
17892	PF1000 IP43 24VDC
17893	PF2000 IP54 24VDC
17894	PF2500 IP54 24VDC
17895	PF3000 IP54 24VDC
17900	PF1000 IP43 230VAC
17901	PF2000 IP54 230VAC
17902	PF2500 IP54 230VAC
17903	PF3000 IP54 230VAC
17904	PF5000 IP54 230VAC
17905	PF6000 IP54 230VAC
17906	PF1000 IP43 115VAC
17908	PF2000 IP54 115VAC
17909	PF6000 IP54 400VAC/3
17910	PFA1000 IP43
17911	PFA2000 IP54
17912	PFA3000 IP54
17913	PFA6000 IP54
17916	18611600000 (dimensions filtre 85x85mm)
17917	18611600000 (dimensions filtre 115x115mm)
17918	18611600000 (dimensions filtre 210x210mm)
17919	18611600000 (dimensions filtre 277x277mm)
17927	PFA2000 IP55
17928	PFA3000 IP55
17929	PFA6000 IP55
17933	PF2000 IP55 230VAC
17934	PF2500 IP55 230VAC
17935	PF3000 IP55 230VAC
17936	PF5000 IP55 230VAC
17937	PF6000 IP55 230VAC
17938	PF2000 IP55 115VAC
17939	PF6000 IP55 400VAC/3
17942	PF1000 IP43 48VDC
17966	PF2000 IP54 48VDC
17969	PF2500 IP54 48VDC
17974	PF3000 IP54 48VDC
17990	PF2000 IP54 CEM 230VAC
17991	PF2500 IP54 CEM 230VAC
17992	PF5000 IP54 CEM 230VAC
17996	PFA2000 IP54 CEM
17997	PFA2500/3000 IP54 CEM
17998	PFA5000/6000 IP54 CEM

**Tableau n°2 : Classement par Indice de Protection**

Références SAREL	Références PFANNENBERG
<b>IP54</b>	<b>IP54</b>
<b>Ventilateurs 24V DC</b> 17892 17893 17894 17895	<b>Ventilateurs 24V DC</b> PF1000 24DC IP43 PF2000 24DC IP54 PF2500 24DC IP54 PF3000 24DC IP54
<b>Ventilateurs 48V DC</b> 17942 17966 17969 17974	<b>Ventilateurs 48V DC</b> PF1000 48DC IP43 PF2000 48DC IP54 PF2500 48DC IP54 PF3000 48DC IP54
<b>Ventilateurs 115V AC</b> 17906 17908 17883 17884 17885 17886	<b>Ventilateurs 115V AC</b> PF1000 115AC IP43 PF2000 115AC IP54 PF2500 115AC IP54 PF3000 115AC IP54 PF5000 115AC IP54 PF6000 115AC IP54
<b>Ventilateurs 230V AC</b> 17900 17901 17902 17903 17904 17905	<b>Ventilateurs 230V AC</b> PF1000 230AC IP43 PF2000 230AC IP54 PF2500 230AC IP54 PF3000 230AC IP54 PF5000 230AC IP54 PF6000 230AC IP54
<b>Ventilateur 400V AC/3</b> 17909	<b>Ventilateur 400V AC/3</b> PF6000 400AC/3 IP54
<b>Grilles de sortie</b> 17910 17911 17912 17913	<b>Grilles de sortie</b> PFA1000 IP43 PFA2000 IP54 PFA2500/3000 IP54 PFA5000/6000 IP54
<b>IP55</b>	<b>IP55</b>
<b>Ventilateurs 115V</b> 17938 17887 17889 17890 17891	<b>Ventilateurs 115V</b> PF2000 115AC IP55 PF2500 115AC IP55 PF3000 115AC IP55 PF5000 115AC IP55 PF6000 115AC IP55
<b>Ventilateurs 230V AC</b> 17933 17934 17935 17936 17937	<b>Ventilateurs 230V AC</b> PF2000 230AC IP55 PF2500 230AC IP55 PF3000 230AC IP55 PF5000 230AC IP55 PF6000 230AC IP55
<b>Ventilateur 400V AC/3</b> 17939	<b>Ventilateur 400V AC/3</b> PF6000 400AC/3 IP55
<b>Grilles de sortie</b> 17927 17928 17929	<b>Grilles de sortie</b> PFA2000 IP55 PFA2500/3000 IP55 PFA5000/6000 IP55

Références SAREL	Références PFANNENBERG
<b>C.E.M. IP54</b>	<b>C.E.M. IP54</b>
<b>Ventilateurs 230V</b> 17990 17991 17992	<b>Ventilateurs 230V</b> PF2000 230AC CEM IP54 PF2500 230AC CEM IP54 PF5000 230AC CEM IP54
<b>Grilles de sortie</b> 17996 17997 17998	<b>Grilles de sortie</b> PFA2000 CEM IP54 PFA2500/3000 CEM IP54 PFA5000/6000 CEM IP54
<b>Filtres</b>	<b>Filtres</b>
<b>filtre standard IP54</b> 17916 (pour grille dimensions 105x105mm) 17917 (pour grille dimensions 150x150mm) 17918 (pour grille dimensions 250x250mm) 17919 (pour grille dimensions 325x325mm)	<b>filtre standard IP54</b> 18611600000 (dimensions filtre 85x85mm) 18611600003 (dimensions filtre 115x115mm) 18611600008 (dimensions filtre 210x210mm) 186116000013 (dimensions filtre 277x277mm)
	<b>filtre IP55</b> 18611600005 (dimensions filtre 115x115mm) 18611600010 (dimensions filtre 210x210mm) 18611600015 (dimensions filtre 277x277mm)