



UKCA CERTIFICATE

APPROVED BODY NUMBER 0843

UK CERTIFICATE OF CONSTANCY OF PERFORMANCE CERTIFICATE No. 0843-CPR-1069

This is to certify that UL International (UK) Ltd. did undertake the relevant AVCP procedures for the equipment identified below which was found to be in compliance with the Construction Products Regulation 2011 as amended by the Construction Products (Amendment etc.) (EU Exit) Regulations 2019 and the Construction Products (Amendment etc.) (EU Exit) Regulations 2020, subject to any conditions attached hereto.

Manufacturer: Pfannenberg GmbH

Address: Werner-Witt-Str. 1, 21035 Hamburg - Germany

Authorised Pfannenberg (UK) Ltd.

Representative: Unit 6C, Aspen Court, Bessemer Way, Centurion Business Park

S60 1FB Templeborough, Rotherham

Product Description: Fire detection and fire alarm systems - Sounder

Model Reference: PA 10 (24 / 48)Vdc

PA 20 (24 / 48)Vdc

Places of production: Same as Manufacturer

Designated Standard(s): EN 54-3: 2001 + A1:2002 + A2:2006

Fire detection and fire alarm systems - Part 3: Fire alarm devices -

Sounders.

This certificate attests that all provisions concerning the assessment and verification of constancy of performance described in Annex ZA of the above referenced standards, under system 1/1+ for the performance set out in this certificate are applied and that the factory production control conducted by the manufacturer is assessed to ensure the constancy of performance of the construction product.

This certificate will remain valid as long as neither the harmonised standard, the construction product, the AVCP methods nor the manufacturing conditions in the plant are modified significantly, unless suspended or withdrawn by the UK Approved body.

Date of 1st issue: 18th October 2022

Issue: 1
Date of re-issue: N/A

Issued by UL International (UK) Ltd., Approved Body 0843.

Name: Richard Bristow

Signed:

Head of Approved Body





UKCA CERTIFICATE

Schedule for certificate No. 0843-CPR-1069

Detailed information sheet

Model Reference: PA 10 (24 / 48)Vdc

Type: Type B

Description: Alarm Sounder

Key Performance parameters: Operating Voltage: 18 - 60 Vdc

Wattage: 9W

Model Reference: PA 20 (24 / 48)Vdc

Type: Type B

Description: Alarm Sounder

Key Performance parameters: Operating Voltage: 18 - 60 Vdc

Wattage: 27W

The following tone selects have been certified:

Tone 2: Descending Tone, 1200/500Hz @1Hz

Tone 15: Ascending Tone, 500 to 1200Hz within 3.5s (0.5s off)

Tone 60: Continuous Tone, 825Hz

Tone 104: Interrupted Tone, 660Hz (150ms on, 150ms off)
Tone 131: Alternating Tone, 800/1000Hz (250ms / 250ms)
Tone 146: Alternating Tone, 554Hz(100mS)/440Hz (400mS)

Technical documentation:

UL Report: NC33054-D03-European Directive-Original

Limitations on the acceptance or use of the product(s):

Installation instructions

To be used in accordance with the supplier's installation instructions.

Terms and Conditions:

- 1. This certificate remains the property of UL International (UK) Ltd, herein "UL UK", and will be withdrawn if any conditions attached to its issue are not complied with.
- 2. This certificate is issued subject to the Global Services Agreement (GSA) and UKCA CPR Service Terms.
- 3. Production is limited to the site(s) as listed, or detailed within the Technical documentation held by UL UK.
- 4. Any product change, production/process changes, etc. which may affect conformity shall be notified to UL UK.
- 5. This certificate is only valid for placing goods on the market of United Kingdom excluding Northern Ireland.

END OF CERTIFICATE

Date of 1st issue: 18th October 2022

Issue: 1
Date of re-issue: N/A

Issued by UL International (UK) Ltd., Approved Body 0843.

Name: Richard Bristow

Signed:

Head of Approved Body

Page 2 of 2