



APPROVED BODY NUMBER 0843

UK CERTIFICATE OF CONSTANCY OF PERFORMANCE CERTIFICATE No. 0843-CPR-1071

This is to certify that UL International (UK) Ltd. did undertake the relevant AVCP procedures for the equipment identified below which was found to be in compliance with the Construction Products Regulation 2011 as amended by the Construction Products (Amendment etc.) (EU Exit) Regulations 2019 and the Construction Products (Amendment etc.) (EU Exit) Regulations attached hereto.

Manufacturer:	Pfannenberg GmbH
Address:	Werner-Witt-Str. 1, 21035 Hamburg - Germany
Authorised Representative:	Pfannenberg (UK) Ltd. Unit 6C, Aspen Court, Bessemer Way, Centurion Business Park S60 1FB Templeborough, Rotherham
Product Description:	Fire detection and fire alarm systems – Visual Alarm Device
Model Reference:	PY X-M-05-SSM PY X-M-10-SSM
Places of production:	Same as Manufacturer
Designated Standard(s):	EN 54-23: 2010 - Fire detection and fire alarm systems – Visual Alarm Device

This certificate attests that all provisions concerning the assessment and verification of constancy of performance described in Annex ZA of the above referenced standards, under system 1/1+ for the performance set out in this certificate are applied and that the factory production control conducted by the manufacturer is assessed to ensure the constancy of performance of the construction product.

This certificate will remain valid as long as neither the harmonised standard, the construction product, the AVCP methods nor the manufacturing conditions in the plant are modified significantly, unless suspended or withdrawn by the UK Approved body.

Date of 1st issue:18th October 2022Issue:1Date of re-issue:N/AIssued by UL International (UK) Ltd., Approved Body 0843.

Them

Richard Bristow Head of Approved Body

Page 1 of 2

UL International (UK) Limited Kingsland Business Park, Unit 1-3 Horizon, Wade Rd., Basingstoke. RG24 8AH United Kingdom

Signed:

Name:

0843-CPR-1071.Docx 27-CP-F0855-Issue 5.0 © UL International (UK) Ltd.



UKCA CERTIFICATE

Schedule for certificate No. 0843-CPR-1071

Detailed information sheet

Model Reference: Type: Description: Key Performance parameters:	PY X-M-05-SSM Type B Visual Alarm Device Operating Voltage: 24 Vdc (18-30Vdc) Wattage: 6.7W Synchronized Flash Mode: 0.5Hz, 0.75Hz, 1Hz Flash Energy: 5J Beacon Category: O* Lens Color: clear, red
Model Reference: Type: Description: Key Performance parameters:	PY X-M-10-SSM Type B Visual Alarm Device Operating Voltage: 24 Vdc (18-30Vdc) Wattage: 13W Synchronized Flash Mode: 0.5Hz, 0.75Hz, 1Hz Flash Energy: 10J Beacon Category: O* Lens Color: clear, red

*VAD Coverage Volume: For details refer to document 30360-005-1-a

Technical documentation:

UL Report:

NC33054-D01-European Directive-Original

Limitations on the acceptance or use of the product(s):

Installation instructions

To be used in accordance with the supplier's installation instructions.

Terms and Conditions:

0843-CPR-1071.Docx

27-CP-F0855-Issue 5.0

© UL International (UK) Ltd.

- 1. This certificate remains the property of UL International (UK) Ltd, herein "UL UK", and will be withdrawn if any conditions attached to its issue are not complied with.
- 2. This certificate is issued subject to the Global Services Agreement (GSA) and UKCA CPR Service Terms.
- 3. Production is limited to the site(s) as listed, or detailed within the Technical documentation held by UL UK.
- 4. Any product change, production/process changes, etc. which may affect conformity shall be notified to UL UK.
- 5. This certificate is only valid for placing goods on the market of United Kingdom excluding Northern Ireland.

END OF CERTIFICATE

Page 2 of 2

Date of 1st issue:18th October 2022Issue:1Date of re-issue:N/AIssued by UL International (UK) Ltd., Approved Body 0843.

Signed: Name:

Richard Bristow Head of Approved Body

UL International (UK) Limited Kingsland Business Park, Unit 1-3 Horizon, Wade Rd., Basingstoke. RG24 8AH United Kingdom