



## **UKCA CERTIFICATE**

# **APPROVED BODY NUMBER 0843**

# UK CERTIFICATE OF CONSTANCY OF PERFORMANCE CERTIFICATE No. 0843-CPR-1064

This is to certify that UL International (UK) Ltd. did undertake the relevant AVCP procedures for the equipment identified below which was found to be in compliance with the Construction Products Regulation 2011 as amended by the Construction Products (Amendment etc.) (EU Exit) Regulations 2019 and the Construction Products (Amendment etc.) (EU Exit) Regulations 2020, subject to any conditions attached hereto.

Manufacturer: Pfannenberg GmbH

Address: Werner-Witt-Str. 1, 21035 Hamburg - Germany

Authorised Pfannenberg (UK) Ltd.

Representative: Unit 6C, Aspen Court, Bessemer Way, Centurion Business Park

S60 1FB Templeborough, Rotherham

Product Description: Fire detection and fire alarm systems – Visual Alarm Device

Model Reference: PY X-S-05-SSM

PY X-S-05

Places of production: Same as Manufacturer

Designated Standard(s): EN 54-23: 2010 - Fire detection and fire alarm systems – Visual Alarm

**Device** 

This certificate attests that all provisions concerning the assessment and verification of constancy of performance described in Annex ZA of the above referenced standards, under system 1/1+ for the performance set out in this certificate are applied and that the factory production control conducted by the manufacturer is assessed to ensure the constancy of performance of the construction product.

This certificate will remain valid as long as neither the harmonised standard, the construction product, the AVCP methods nor the manufacturing conditions in the plant are modified significantly, unless suspended or withdrawn by the UK Approved body.

Date of 1st issue: 18th October 2022

Issue: 1
Date of re-issue: N/A

Issued by UL International (UK) Ltd., Approved Body 0843.

Signed: V Name: Rie

Richard Bristow

Head of Approved Body





# **UKCA CERTIFICATE**

## Schedule for certificate No. 0843-CPR-1064

#### **Detailed information sheet**

Model Reference: PY X-S-05-SSM

Type: Type B

Description: Visual Alarm Device

Key Performance parameters: Operating Voltage: 24 Vdc (18-30 Vdc)

Wattage: 9.5W Flash Mode: 1Hz Beacon Category: O Lens Color: clear, red

Model Reference:

Type:

Type B

Description:

PY X-S-05

Type B

Visual Alarm Device

Description: Visual Alarm Device
Key Performance parameters: Operating Voltage: 24 Vdc Operating

Performance parameters: Operating Voltage: 24 Vdc Operating Voltage: 48 Vdc (18-30 Vdc) (40-60 Vdc) Wattage: 9.5W Wattage: 7.5W

Flash Mode: 1Hz Beacon Category: O Lens Color: clear, red

## **Technical documentation:**

UL Report: NC33054-D01-European Directive-Original

## Limitations on the acceptance or use of the product(s):

Installation instructions

To be used in accordance with the supplier's installation instructions.

### **Terms and Conditions:**

- 1. This certificate remains the property of UL International (UK) Ltd, herein "UL UK", and will be withdrawn if any conditions attached to its issue are not complied with.
- 2. This certificate is issued subject to the Global Services Agreement (GSA) and UKCA CPR Service Terms.
- 3. Production is limited to the site(s) as listed, or detailed within the Technical documentation held by UL UK.
- 4. Any product change, production/process changes, etc. which may affect conformity shall be notified to UL UK.
- 5. This certificate is only valid for placing goods on the market of United Kingdom excluding Northern Ireland.

**END OF CERTIFICATE** 

Date of 1st issue: 18th October 2022

Issue: 1
Date of re-issue: N/A

Issued by UL International (UK) Ltd., Approved Body 0843.

Name: Richard Bristow

Signed:

Head of Approved Body

Page 2 of 2