Pfire Sounder
NS100 103 db(A)



- Efficient – Particularly low power consumption for enhanced efficiency
- Simple – Quick and easy mounting to minimize installation costs
- Safe – Line monitoring via polarity reversal possible
- Flexible – Allows synchronous operation across the entire product family
- Versatile – Also available as a sounder/LED combination

EN 54-3

IP 65
Degree of protection


+70 °C
–25 °C
Operating-temperature


3D-COVERAGE PERFORMANCE DATA		NS100
AUDIBLE	75 dB (A)	21 x 15 x 8 m @DIN tone
	80 dB (A)	12 x 8 x 4 m @DIN tone
	85 dB (A)	7 x 5 x 2 m @DIN tone


To determine the exact signalling area for your needs, please use the online available Pfannenberg Sizing Software PSS.


PRODUCT	NS100
DATA	
Operating range	18 - 56 V DC
Nominal current consumption @DIN-tone	25 mA
Sound pressure level @DIN-tone	103 dB(A)
Alarm tones	32 selectable
Operating temperature	–25 °C ... +70 °C
Degree of protection	IP65
Material	ABS / PC
Connecting terminals	0,28 - 2,5 mm²
Weight	225 g

DIMENSIONS MM









ARTICLE NR.	NS100
	23280630010