

## HPR Series -HOSE-PROOF RAINHOOD

The **HPR (Hose-Proof Rainhood)** product series serves as an accessory which, in combination with filter fans, prevents even jet water or heavy rain from entering an enclosure.

If control cabinets are cleaned with high-pressure cleaners or are exposed to strong weather with a lot of rain in outdoor areas, this additional **protection of the enclosure** is recommended.

#### **BENEFITS:**

- Very shallow depth, thus less space required to the outside. This keeps escape and traffic routes free. Several tests have proven that the depth was reduced only to the extent that the airflow was not impaired.
- Very user-friendly installation by sliding the hood onto the basic housing, which is screwed to the control cabinet as usual.
- High protection against vandalism due to impact resistance IK10 and optional screwing of the hood from the inside. This means that it is not possible to unscrew the screws from the outside.
- The **filter mats** of the rear filter fan/exhaust filter can be **easily replaced**.
- With **UL certification**.
- With IP X6 and NEMA 1, 12, 3R, 4X in connection with filterfan.
- In addition to the standard stainless steel version, Pfannenberg also offers a **powder-coated steel version (RAL 7035)**.
- The use of brushed V2A stainless steel allows a **seamless design** with existing stainless steel cabinets and increases **corrosion resistance**.





#### **TARGETED APPLICATIONS / INDUSTRIES**

- Outdoor applications in public areas
- All industrial enclosures that need to be covered, where it is necessary to allow air exchange through the opening, but at the same time to provide protection against water jets/heavy rainfall

More information about the product series on our website.



# **Pfannenberg Solutions**

HPR Series

#### **TECHNICAL DATA:**


The HPR series is available in three different sizes in two designs, which can be combined with our Pfannenberg fourth generation filterfan portfolio (PF 11.000 - PF 67.000).

Produkt	H x W x D [mm]	Article no.	Certification	Fitting
HPR 20.000	260 x 220 x 38	18112000000 (RAL 7035)	NEMA 1, 12	- Size 1 & 2
		18112000001 (V2A)	NEMA 1, 12, 3R, 4X	
HPR 40.000	400 x 330 x 38	18112000002 (RAL 7035)	NEMA 1, 12	- Size 3 & 4
		18112000003 (V2A)	NEMA 1, 12, 3R, 4X	
HPR 60.000	485 x 400 x 100	18112000004 (RAL 7035)	NEMA 1, 12	- Size 6
		18112000005 (V2A)	NEMA 1, 12, 3R, 4X	

#### **MOUNTING:**

By simply sliding on and screwing (optional), the installation of the bonnets is very simple and safe.







### Service and Contact



#### Global technical Service

24/7 worldwide presence | commissioning, repair and mainternance | F-GAS leakage tests | spare part kits | service trainings | PSS - Pfannenberg Sizing Software



Simply scan the QR code and find the nearest Pfannenberg branch office