PY X-S-05-PL

PYRA XENON FLASH LIGHT 5J 18CD

24VDC RAL7035 RD

CE marked - complete | EurAsian Conformity | UL listed | 10 years warranty | Effective Planning


Shape-moulded gasket staying perfectly in place
Ensuring fast and secure installation

Flexible mounting
Usable in any operating position

High-quality components
Ensuring long life with 70% light output even after 8 million flashes

Performance Level C
Fulfilling functional safety requirements

Powerful xenon flash
High signaling effect and large coverage



PY X-S-05-PL	Item number 21510805008
Rated voltage range (DC)	24-24
Voltage range (DC)	21.6-26.4
Voltage type	DC
Rated current consumption DC	0.36
Light intensity (cd)	18
lens colour	Red
Type of optical signal	
Function flashing light	Yes (1)
Function blinking light	No (0)
Function continuous light	No (0)
Function rotating light	No (0)
Max. viewing distance (m)	98.34
Lamp type	XENON
Number of flashes until 70% light emission	8000000
Operating temp. range (°C)	-40-55
Max. relative humidity (%)	90
Duty cycle (%)	100
IP protection	66
Protection system (UL 50E / NEMA 250)	Type 4/4X
Mechanical resistance (IEC 62262)	IK08
Colour housing/item	Grey
Housing material	PC/ABS
Material of the lens or dome	PC
Cable entry size	M20
Cable entry quantity	4
Weight of the product (kg)	0.2


Subject to technical amendments and misprints.

PY X-S-05-PL	Item number 21510805008
GTIN (EAN)	4061131273820
ETIM-class 10.0	EC001333
Product dimensions (mm)	86 mm x 110 mm x 81 mm

Subject to technical amendments and misprints.

Pfannenberg 3D - Coverage

Size of visual coverage



VISUAL

Application	Visual coverage area
Indicate	25.2 m x 22.1 m x 27.5 m
Warning	11.2 m x 9.8 m x 12.2 m
Alert	5.6 m x 4.9 m x 6.1 m

To determine the exact signaling area for your needs, please use the online available Pfannenberg Sizing Software PSS.

Accessories	pcs	Item number
Cover for Patrol/Pyra locking elements to prevent unauthorized access	4	28300000002
Sealing mounting surface, 3 mm self-adhesive	1	28300000004
Pyra-S Lens RD 5pcs	1	28112000046
Threaded sleeve brass M20 with gasket for connecting Patrol and Pyra enclosures	1	28300000003
Pyra panel mounting kit for flat installation with touch protection	1	28300000010

For additional models, options and voltages visit www.pfannenberg.com or contact us directly.