# **PTF 1200** FILTERFANS FOR ROOF MOUNTING 1000 m<sup>3</sup>/h

- Air flow rate up to 1000 m3/h
- Protection class IP 54 / NEMA Type 12
- Compact size: this allows the combination of two units on one standard housing
- Energy-efficient EC centrifugal fan
- Full metal housing
- Optimum airflow and uniform temperature distribution (natural convection of the air is supported)
- Easy mounting
- UR approval



| PRODUCT   | PTF 1200  |                    |         |
|---|---|--------------------|---------|
| ARTICLE NO.   | 11692102055                                       | 11692152055        | Unit    |
| DATA  |   |                    |         |
| Rated voltage ±10 %                                     | AC 50   60 Hz                                     |                    |         |
|   | 230   | 115                | V       |
| Unimpeded airflow                                       | 1000  |                    |         |
| Airflow rate in comb.<br>with 2x exhaust filter (IP 55) | 870   |                    | m³/h    |
| Power consumption                                       | 170   |                    | W       |
| Current consumption                                     | 1.40  | 2.20               | A       |
| Noise level according to DIN ISO 13347                  | 74  |                    | dB (A)  |
| Weight  | 6.55  |                    | kg      |
| Type of connection                                      | X-COM plug  |                    |         |
| Fuse  | 6   |                    | A       |
| System of protection according to EN 60529 / UL 50      | IP 54 / NEMA Type 12                              |                    |         |
| Filtration efficiency                                   | 81  |                    | %       |
| Filter mat quality class according to EN 779            | G 4   |                    |         |
| Bearing type  | ball bearing                                      |                    |         |
| Service life L <sub>10</sub> (+ 40 °C) <sup>1</sup>     | approx. 70000                                     |                    | h       |
| Operating temperature                                   | -25 +60   -13 +140                                | −25 +50   -13 +122 | °C I °F |
| Storage temperature                                     | -40 +80 l -40 +175                                |                    |         |
| Design  | sheet steel, powder-coated                        |                    |         |
| Mounting  | Screw mounting on the enclosure roof              |                    |         |
| Colour  | RAL 7035   different colours available on request |                    |         |

| ACCESSORIES   |           | ARTICLE NUMBER |  |  |
|---|-----------|----------------|--|--|
| Spare filter mats   | 20 pieces | 18611600193    |  |  |
| Thermostat  |           | 17121000000    |  |  |
| Hygrostat   |           | 17207000000    |  |  |
| For additional models, options and voltages visit www.pfannenberg.com or contact us directly. |           |                |  |  |

 $<sup>^{1}</sup>$  fan failure is defined as being when the current and speed deviate or the operating noises are out of the ordinary  $^{2}$  L  $_{10}$  (+25  $^{\circ}$  C)







## **Cooling capacity performance curves**


## Static pressure performance curve

## **PTF 1200**





#### **Dimensions**



#### **Cut-out**

