

PEF 180
INTERNAL ENCLOSURE FAN 160 - 170 m³/h

- For long rows of electrical enclosures which are only cooled with one unit.
- All industry applications.
- Distribution of the cold air in the electrical enclosure.
- Used mostly in combination with cooling unit or air/water heat exchangers.



PRODUCT	PEF 180		
ARTICLE NO.	18110000000	18110000002	Unit
DATA			
Rated voltage ±10 %	AC 50 60 Hz	DC	
	230	24	V
Airflow	160	170	m³/h
Power consumption	19 18	5	W
Recommended fuse	max. 6		A
Connection	screw terminal	AWG 22 single wires, TR 64	
Temperature range	-40 ... +55 -40 ... +131		°C °F
Dimensions	161 x 202 x 52	161 x 202 x 46	mm
Weight	916	570	g

