


Shielding effectiveness

PF 11.000 EMC /
PFA 10.000 EMC


Attenuation [dB]



	E-M-field	dummy plate
	H-field	dummy plate
	E-M-field	PFA 10.000
	H-field	PFA 10.000

PF 22.000 EMC /
PFA 20.000 EMC


Attenuation [dB]



	E-M-field	dummy plate
	H-field	dummy plate
	E-M-field	PFA 20.000
	H-field	PFA 20.000

PF 32.000 EMC /
PFA 30.000 EMC


Attenuation [dB]



	E-M-field	dummy plate
	H-field	dummy plate
	E-M-field	PFA 30.000
	H-field	PFA 30.000

PF 42.500 EMC /
PF 43.000 EMC /
PFA 40.000 EMC


Attenuation [dB]



	E-M-field	dummy plate
	H-field	dummy plate
	E-M-field	PFA 40.000
	H-field	PFA 40.000

PF 65.000 EMC /
PF 66.000 EMC /
PF 67.000 EMC /
PFA 60.000 EMC

Attenuation [dB]



	E-M-field	dummy plate
	H-field	dummy plate
	E-M-field	PFA 60.000
	H-field	PFA 60.000